

## VIBRATORY DISC MILL (G-430)

- Used for quick grinding, assuring that no sample loss can be experienced.
- It has a very wide range grinding and finishes the job in an extremely short time.
- The maximum materials feed size is 15 mm and grinds to a final fineness of 50 micron.
- The jar size that is supplied with the equipment is 100 ml.



### ● TECHNICAL SPECIFICATIONS

- Suitable for quick grinding
- No sample loss
- Wide range grinding
- Extremely short grinding time
- Material feed size < 15 mm
- Final Fineness < 50 mic
- Jar Size 100 ml